



Dramatically shorten the attachment and detachment time of material hoses!


Easy hose changeover without tools, contributing to shorter setup times.

When secured, the lock mechanism prevents the hose from coming off even if it is accidentally pulled.

The plug side (pipeless type) can be directly attached to the equipment (for Φ38 attachment).









Rotate the socket side coupler in the direction of the "LOCK" arrow.



Once the **A** marks align, the lock will engage and prevent disconnection.

You can choose parts according to the mounting method and combine them.











Hose identification sticker

With the included identification stickers, you can manage hoses for each resin, making it possible to shorten setup times.

One-Touch Coupler Order Code Table



One-touch Coupler Φ38 Pipe Plug			
N a m e	Order Code	Order Unit	Weight
One-touch Coupler Ф38 Pipe Plug	*HW38-P1	1 piece	35g
	A15P9A01	10-piece set	_



One-touch Coupler Φ38 Hose Plug (with 2 hose bands and 1 one-touch coupler sticker)			
N a m e	Order Code	Order Unit	Weight
One-touch Coupler Φ38 Hose Plug	*HW38-P2	1 piece	142g



One-touch Coupler Φ38 Socket (with 2 hose bands and 1 one-touch coupler sticker)			
N a m e	Order Code	Order Unit	Weight
One-touch Coupler Φ38 Socket	*HW38-S1	1 piece	218g
	A15P09A02	10-piece set	_



One-touch Coupler Φ38 Socket R with Flange (with 2 hose bands, 1 high grip, 1 R flange and 1 one-touch coupler sticker)			
N a m e	Order Code	Order Unit	Weight
One-touch Coupler Φ38 Socket R with Flange	A152P9050	1 piece	218g
One-touch Coupler 438 Socket R with Flange	A15P9A03	10-piece set	_

* Weight does not include accessories


ne-touch Coupler Sticker (Blue, Red, Yellow)			
Name	Order Code	Order Unit	Weight
One-touch Coupler Sticker	*HWS-5269	1 sheet	_

* Caps are also available. Please feel free to contact us if you are interested.

Precautions

* For suction and convaying of resin molding granular materials only (Not for liquids)
* The resin part can be damaged if subjected to impact due to falling, etc.
* When inserting and removing, be careful not to pinch your fingers in the gap See the one-touch coupler tutorial vedio here! between the socket side coupler and the C-type stop ring.

Dimensional drawing



Manufacturer: ISO9001 CERTIFIED INTERNATIONAL MARKETING DEPT. 4124-1,MINAMI-MINOWA KAMIINA-GUN NAGANO-PREF.399-4595 JAPAN TEL.+81-265-73-8820, FAX.+81-265-73-8964

http://www.harmo-net.co.jp

